



Frank Bacon Machinery Sales Company, Inc.

4433 East Eight Mile Road • Warren, MI 48090-0886 • (586) 756-4280 • Fax (586) 756-8009 • Toll Free (800) 394-4280 •

e-mail: sales@frankbacon.com • On The Web: www.frankbacon.com

Stock #: 11289-00

We offer for your consideration, subject to prior sale and conditions stated at the left for immediate acceptance.

Conditions of Sale	Description
--------------------	-------------

TERMS:
30% Deposit with the order, balance before shipment.

We reserve the right to correct typographical errors.

GUARANTEE:
Unless otherwise specified, every machine is offered with the standard **MDNA** (MACHINERY DEALERS NATIONAL ASSOCIATION) Return privilege to ensure your complete satisfaction. If the machine is unsatisfactory it may be returned to our warehouse, freight prepaid and in the original condition within 30 Days of shipment for a full refund less the cost of SPECIALIZED EQUIPMENT, NEW ITEMS AND RE-CERTIFICATION COSTS, When applicable.

Care is taken to provide accurate specifications. However, Critical areas should be verified by Inspection.

WARRANTY:
FBMS Provides a ONE Year parts and labor Warranty on all reconditioned Testers and 90 Days on Reconditioned tools less all travel and/or Shipping Related Expenses. Unless otherwise specified.

MDNA | AMDA
MMA | ASTM | SAE
ASM

(1) **USED Struers Accutom 5**, Digital Microprocessor Controlled Automatic Laboratory Diamond Abrasive Cut-off Saw. S/N 4940042

SPECIFICATIONS:

Cutting Wheel Diameter:	2.95" to 5.98"
Drive Motor:	370W @ 3000RPM
Cutting Wheel Speed (RPM):	300 – 3000 Variable
Sample Feed Rate (In/Sec.):0002 – 0.12 Variable
Sample Feed Force (lbs):	4.5, 9.0 or 13.5
Sectioning Capacity:	3.15" Max. with Rotation
Approximate Dimensions (WxDxH)	20" x 27.5" x 10.6"
Electrical Requirements (V, Hz, PH, Amps):	100 - 120, 50/60, 1, 5.4
Approximate Weight (Lbs.):	100
Utility Requirements:	NA

EQUIPPED WITH:

- Menu Control and Digital Read-Out
- Database with User-definable Cutting Methods
- Sample Rotation or Oscillation
- General Use Vise Type Specimen Holder w/1.57" Opening
- Hood Safety Interlock
- Built-In Recirculating Coolant System

FOB Warren, MI Cleaned & Serviced with Warranty